













SPM2 Poliermaschine SPM2 Polishing Machine

SPM2 Polierfolien SPM2 Polishing films

Artikel-Nr. Part number	Bezeichnung Discription	Bild Graph	Artikel-Nr. Part number	Bezeichnung Discription	Bild Graph
PF10-A010-2000	Polierfolie Aluminiumoxyd, 1 µm, Ø 60 mm Polishing film Aluminium- oxyd, 3 µm, Ø 2,36"		PF10-S160-2000	Polierfolie Siliciumcarbid 16 µm, Ø 60 mm Polishing film Siliciumcarbid 16 µm, Ø 2,36"	
PF10-A010-20K0	Polierfolie Aluminiumoxyd, 1 µm, Ø 60 mm, PSA Polishing film Aluminium- oxyd, 1 µm, Ø 2,36", PSA		PF10-A120-2000	Polierfolie Aluminiumoxyd, 12 µm, Ø 60 mm Polishing film Aluminium- oxyd, 12 µm, Ø 2,36"	
PF10-A030-20K0	Polierfolie Aluminiumoxyd, 3 µm, Ø 60 mm, PSA Polishing film Aluminium- oxyd, 3 µm, Ø 2,36", PSA		PF10-A120-20K0	Polierfolie Aluminiumoxyd, 12 µm, Ø 60 mm, PSA Polishing film Aluminium- oxyd, 12 µm, Ø 2,36", PSA	
PF10-D005-2000	Polierfolie Diamant 0,5 µm, Ø 60 mm Polishing film diamond 0,5 µm, Ø 2,36"		PF10-A300-20K0	Polierfolie Aluminiumoxyd, 30 µm, Ø 60 mm, PSA Polishing film Aluminium- oxyd, 30 µm, Ø 2,36", PSA	
PF10-D030-2000	Polierfolie Diamant 3 µm, Ø 60 mm Polishing film diamond 3 µm, Ø 2,36"		PF40-F002-2000	Polierfolie Final polish, Ø 60 mm Polishing film final polish, Ø 2,36"	
PF10-D005-20K0	Polierfolie Diamant 0,5 µm, Ø 60 mm, PSA Polishing film diamond 0,5 µm, Ø 2,36", PSA		PF10-S300-20K0	Polierfolie Siliciumcarbid 30 µm, Ø 60 mm, PSA Polishing film Siliciumcarbid 30 µm, Ø 2,36", PSA	

Achtung: geänderte Artikelnummern / Attention: changed part numbers

10/2020